

Groen Vacuum Flash Chamber System

Mfg: Groen

Model: Flash Chamber

Stock No.: G116-BC

Serial No.: 83196

Groen Vacuum System. Previously used as a deodorizer. Model: Flash Chamber. S/N: 83196. MAWP: 50 psi. Groen Vertical Separator- 20 Gallon, inside straight-wall dimensions: 1 ft. 5 in. dia. x 1 ft. 9 in. H, CIP sprayballequipped. Inlets: (1) 2 in. dia. S-line fitting. Outlets: (1) 1-1/2 in. dia. S-line fittings. Media: (1) 1 in. dia. Sline fittings. Overall dimensions: 6 ft. 6 in. L x 2 ft. 6-1/2 in. W. 8 ft. 3 in. H.

Vapor Condenser: Ametek Shell and Tube Heat Exchanger. S/N: WL-5125. Type: AHT-4-A-SS. Size: 4-7-36. Single pass. Number of tubes: 52. Tube dimensions: 1/2 in. dia. x 2 ft. 11 in. L. Heat transfer surface area: approx. 19.84 sq. ft. Capacity: 1.5 gal. Shell side MAWP: 240 psi @ 600 °F. Inlets: (1) 2 in. dia. S-line fitting (product), (1) 1-1/2 in. dia. S-line fitting (media). Outlets: (1) 2 in. dia. S-line fitting (product), (1) 1-1/2 in. dia. S-line fitting (media).

Product Recirculation Pump: G&H Positive Displacement Pump, Model: 432, S/N: 93-2-41824. Sew-Eurodrive Motor, 2 hp, 460/2290 rpm, 208/360 V, 6.72/3.88 amps, 60 Hz, 3 phase. Sew-Eurodrive Variable Speed Drive, ratio: 4.47, rpm (min/max): 104/515. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings.

Vacuum Pump with Marathon Electric Motor, 2 hp, 3470 rpm, 208-230/460 V, 5.4/2.7 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Research Control Valve, Model: 1017, S/N: 191715, ACT: ATO, sig: 3-15, trim: H. Inlets/outlets: (2) 1 in. dia. FNPT fittings.

















