

## Tri-Clover Diaphragm Partial Pump

Mfg: Tri-Clover

Model: C328

Stock No. GAWD005.4a

Serial No.

Tri-Clover Diaphragm Partial Pump. Model: C328. 316 stainless steel construction. Maximum flow rate: 156 gpm. Maximum size solids: 1/4 in. Maximum suction lift: 24 ft. Inlets/outlets: 2-1/2 triclamp fittings. Overall dimensions: 16 in. L x 13 in. W x 16 in. H.

