

Howe 6-Cylinder Reciprocating Compressor

Mfg: Howe Corp.

Model: J56

Stock No.: HCJM03.6

Serial No.:

Howe Reciprocating Compressor. Model J-56. Markings: 540-A-2, 53 A-3. Refrigerant: NH4 / R-717, ammonia. Number of cylinders: 6. Water cooled heads. Zero hours since factory rebuild. Nominal rating at 1200 RPM (ammonia): 121.2 TR / 135.6 BHP at +20F suction / 96.2F condensing. Nominal rating at 1200 RPM (R-22 freon): 111.20 TR / 130 BHP at +20F suction / 95F condensing. Max pressure differential: 175 PSIG. Max discharge temp: 300F. Weight: 2,800 lbs. Dimensions: 56 L x 56 W x 46 H (inches).





