

Crepaco R4RT Positive Displacement Pump

Mfg: Crepaco

Model: R4RT

Stock No. HD126.

Serial No. D-3666

Crepaco R4RT Positive Displacement Pump. Model: R4RT. S/N: D-3666. Maximum Capacity: 90 Gpm. Displacement: 17.50 Gpm/100 Revs. Maximum power: 20 BHP. Max. Rpm: 900. The pump is known for their rugged, long-lasting and efficient performance. It has a standard stainless steel body, resilient molded rotors, and a heavy duty cast iron gear case which provides long-lasting, economical service over a wide range of products and applications. Easy disassembly and cleanup, low maintenance. Typical applications: fruit cocktail, yogurt, alcoholic beverages. Inlet: (1) 9-1/4 in. L x 1-3/4 in. W. Overall Dimensions: 15-1/4 in. L x 14-1/4 in. W x 8-1/2 in. H.



