

2004 Siemens 4160V Motor- 600 HP

Mfg: Siemens

Model:

Stock No: HDAF763.22a

Serial No: E17097-02-3

2004 Siemens 4160V Motor- 600 HP. S/N: E17097-02-3. Type: CG. Motor specifications: 3564 rpm, 4160 V, 73.1 amps, 60 Hz, 3 phase. Frame: 508S. Insul. class: F. Rotation: CCW A-T. Facing: B-T2. Drive End: C-T3. With CWA-T. Phase: B-T2. Service Factor: 1.15. KVA Code: G. Shaft size: 3 in. Bearing type: Ball. Overall dimensions: 46-1/2 in. L x 50 in. x W x 26 in. L.



SIEMENS

Induction Motor

SER. NO.	27087-02-3	TYPE	CG	FLY	CG
H.P.	1/2	FRAME	508S	FLY	CG
AMPS	12.1	VOLTS	480	FLY	CG
R.P.M.	1725	HERTZ	60	FLY	CG
DUTY	100%	°C	PHASE 3	FLY	CG
INS.	100%	100%	100%	FLY	CG

ROTATION	FACING	DRIVE END	WITH	PHASE -	SEQUENCE A-B-C
CCW A-T	B-T2	C-T	CW A-T	B-T2	C-T

Siemens Energy & Automation, Inc. Norwood Ohio Made in U.S.A.