

Cherry-Burrell Superhomo Homogenizer

Mfg: Cherry-Burrell

Model: SS-3000 SGR

Stock No.: HDAF954A.11a

Serial No.: 79010

Cherry-Burrell Superhomo Homogenizer. Model: SS-3000 SGR. S/N: 79010. Maximum capacity: 1630 gph. Minimum capacity 1500 gph. Single-stage manual valve assembly. Plunger size: 1-7/8 in. dia. Poppet seat valve cylinders. Maximum operating pressure: 2500 psi. Motor. Motor pulley diameter: 7-1/2 in. Gear pulley diameter: 1 ft. 5 in. Inlets: (1) 2-1/2 in. dia. ACME fitting. Outlets: (1) 2-1/2 in. dia. female I-line fitting (reduces to 1 in.). Overall dimensions: 4 ft. 4 in. L x 3 ft. 1 in. W x 3 ft. 11 in. H. (ACN610).



