

## Sweco 24 in. Vibra-Energy Sifter with 40 Gallon Receiving Tank.

Mfg: Sweco

Model:

Stock No. HDBA078.16.

Serial No.

Sweco 24 in. Vibra-Energy Sifter with 40 Gallon Receiving Tank. Sifter and tank are frame-mounted. Sifter opening is 22-1/2 in. dia. x 3 in. H. Sifter is equipped with one sifting level of stainless steel 16-mesh. Bottom base is 22-1/2 in. dia. x 3 in. H. Silting levels are supported by (12) 1-1/4 in. dia. springs. Sifter inlets/outlets: (2) 6 in. discharge outlets. Receiving tank has a 24 in. dia. opening. Tank inlets/outlets: (1) 2 in. dia. central outlet, (1) 3 in. dia. side inlet. Baldor Industrial Motor, 1/3 hp, 1,140 rpm, 220 V, 1.2 amps, 60 cycles, 3 phase. Overall dimensions: 48 in. L x 26 in. W x 52-1/2 in. H.



