

Bean Royal High Pressure Pump

Mfg: Bean Royal

Model: R-35

Stock No. HDBA085.3a

Serial No. 22618

Bean Royal High Pressure Pump. Model: R-35, S/N: 22618. Capacity: 35 gpm. 700 psi.
Inlets/outlets: (1) 2 in., (1) 1.5 in. Johnny Electric Motor: 10 hp, 1,735 rpm, 220 V, 26 amps, 60 Hz, 3 phase. (6) Ball valves: 1.2 in. dia. 2.5:1 pulley ratio. Overall dimensions: 61 in. L x 34 in. W x 48 in. H. New cost approximately: \$5,000.

