

Cherry-Burrell Stellar Series Homogenizer - 3000 PSI

Mfg: Cherry-Burrell

Model: SS-3000-SGR

Stock No.: 145.HDCC82.52a

Serial No.: 278231

Cherry-Burrell Stellar Series Superhomo Homogenizer. Model: SS-3000-SGR. SN: 278231. Plunger size: 1-5/8 inch. Capacity: 1500 GPH. Block S/N's: H 144 /4493880 /1926. Single stage valve assembly. Poppet seat valve cylinders. Maximum operating pressure: 3000 psi. U.S. Electric Motor, 50 hp, 1775 rpm, 230/460 V, 118/59 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. ACME fitting. Outlets: (1) 2 in. dia. ACME fitting (reduces to 3/4 in.). Overall dimensions: 4 ft. 3 in. L x 3 ft. W x 4 ft. 7 in. H.



