

Crepaco R4R Positive Pump

Mfg: Crepaco

Model:

Stock No. HDDF078.2a

Serial No. A4558

Crepaco R4R Positive Pump. Size: R4R. S/N: A4558. Current capacity at max/min drive rpm: 90/18.2 gal. Maximum capacity: 90 gpm. Maximum speed: 900 rpm. Reliance Electric motor, 1750rpm, 230/460 V, 26/13 amps, 60 Hz, 3 phase. Reeves motor drive, size: 331, ratio: 6.2, 7-1/2 hp, output speeds: 520 rpm maximum, 104 rpm minimum. Complete parts interchangeability. Easy disassembly and cleanup, low maintenance. Typical applications: fruit cocktail, yogurt, alcoholic beverages, doughs, chocolate and shampoo. Start/stop switch. Pump inlet/outlets: 2 in. $\frac{1}{2}$ in. Overall dimensions: 45 in. L x 45 in. W x 36 in. H.



