

Westinghouse Motor – 15 HP

Mfg: Westinghouse


Model: LR96872

Stock No: HDDG406C

Serial No:

Westinghouse Motor. Model: LR96872. 15 hp, 1760rpm, 230/460V, 38/18A, 60 Hz, 3 phase. Shaft length: 4-1/4 in. Shaft diameter: 1-1/2 in. Overall dimensions: 2 ft. L x 17 in. W x 13 in. H.





W		OPTIM		LR96872		RU	
15 HP		4 P		FRAME 254T	PHASE 3	HERTZ 60	TEFC
RPM	1760	DESIGN	B	AMB	40°C	C.O.D. NO.	
INS. CL.	F	VOLTS	230 / 460		4	9	6
KVA CODE	G	AMPERES	36 / 18		8	5	7
S.F.	1.15	USEABLE ON 208 VOLT NETWORK AT 41 AMPS		2	3	1	
RATING CONT.				1	1		
NOM. EFF.	87.5	MIN. EFF.			330V LINE		460V LINE
CAT. NO.	501504TE			330V LINE		460V LINE	
DRIVE BRG.	6309Z2			CODE BRG.		6307Z2	
SERIAL NO.							

Westinghouse ENERGY EFFICIENT AC MOTOR

WESTINGHOUSE MOTOR CO. 1000 WESTINGHOUSE BLVD. PITTSBURGH, PA. 15222