

Hosokawa Bepex Rietz Angle Disintegrator- 15 HP

Mfg: Hosokawa Bepex Rietz

Model: RP12-k122

Stock No. HDOC170.45

Serial No. RP84001760

Hosokawa Bepex Rietz Angle Disintegrator- 15 HP. Model RP12-k122, S/N: RP84001760. Screen and hammers: 304 stainless steel. Housing: 316 stainless steel. Equipped with (7) 11-7/8 in. dia. x 1-1/2 in. W hammers. Perforation type: round. One-piece circular screen size: 3/4 in. dia. x 6 in. H. Standard RP model disintegrator with cover held by Vee band clamp. Maximum internal pressure rating: 4 psig. Hosokawa Bepex Motor, 15 hp, 1765 rpm, 230/460 V, 36/18 amps, 60 Hz, 3 phase. Inlets: (1) 11-1/2 in. dia. hopper with 16 in. dia. flange and (4) 3/8 in. dia. attachment holes at a center-to-center distance of 15-1/4 in. Outlets: (1) 20 in. W x 4 in. H discharge chute. Overall dimensions: 33 in. L x 28 in. W x 36 in. H.



