

Lee Jacketed Kettle 100 Gallon

Mfg: Lee

Model:

Stock No. HDPH108.5a

Serial No. 97M

Lee Jacketed Kettle 100 Gallon.

Stainless steel. S/N 97M. (2) Removable hinged lids. Inside dimensions: 36 in. dia. x 31 in. H. Hemispherical bottom is jacketed. Kettle has a MAWP of 40 psi, MAWT of 290 Degrees Fahrenheit, Hydrostatic Test Pressure of 80. Kettle agitator has (8) 3-1/2 in. L x 3-1/2 in. W. Scrapers. Jacket inlets: (3) 1 in. NPT Threaded Pipes. Kettle has 3 in. center outlet. 2 hp Sew Eurodrive Motor, 1,720 rpm, 230/460 V, 6.2/3.10 amps, 60 Hz, 3-phase. Sew Eurodrive Motor Drive, 36.83 Gear Ratio, 1,720 rpm (in), 47 rpm (out), 2700 lb-in. Torque. Overall Dimensions: 42 in. L x 41-1/2 in. W x 76-1/2 in. H. Unit has been pressure tested.



