

Tri Clover Pump

Mfg: Tri Clover

Model: SP-218M-9237-35

Stock No. HDPH253D.6

Serial No. WO926

Tri Clover Pump. Model: SP218M-9237-35. S/N: W0926. Capacity: up to 300 gpm @ 70 psi and 170 tdh. Impeller diameter: 7 in. Seal option: double mechanical seals with water flush. Reliance Electric XE Motor, 25 hp, 3535 rpm, 230/460 V, 58.2/29.1 amps, 60 Hz, 3 phase. Pump is suitable for CIP-applications. For sanitary hygienic applications such as pharmaceutical, biotechnology, fine chemical, food, beverage, and dairy. Inlets: (1) 1 in. dia. S-line, (1) 3 in. S-line. Outlets: (1) 1-1/2 in. S-line Outlets. Overall dim: 51 in. L x 22 in. W x 22 in. H.



