

## Albin Positive Displacement Pump

Mfg: Albin

Model: SLP 115 P51 A31 B1 AOT

Stock No.: HDPH253L.4a

Serial No.: 141452

Albin Positive Displacement Pump. Model: SLP 115 P51 A31 B1 AOT. S/N: 141452. Flow rate for new pump is 24.5 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Pump is controlled by an Amicon motor control system which provides for: variable speed control, (4) limit control, and rotation reversal. Danfoss DC motor, 3 hp, 1750 rpm, 0-180 VDC, 14.0 amps. Driver pulley diameter: 3 in. Driven pulley diameter: 5 in. Ratio: 1.666:1. Final rpm: 1050 (max). Inlets/Outlets: (2) 1-1/2 in. S-Line fittings. Overall dimensions: 3 ft. 1 in. L x 1 ft. 10 in. W x 3 ft. H.(ACN65a).









