

Mojonnier Dome-Top Jacketed Pressure Wall Processor Tank- 1200 Gallon

Mfg: Mojonnier

Model:

Stock No. HDTD051.8a

Serial No.

Mojonnier Dome-Top Jacketed Pressure Wall Processor Tank- 1200 Gallon. 304 Stainless steel construction. Inside dimensions: 72 in. dia. x 66 in. H. Features include: (1) 16 in. dia. manway with sight glass, dual sprayballs, (1) 4 in. dia. sight glass, front access ladder with step platform and a side and bottom sweep agitator with baffle. Tank has a convex bottom. Mojonnier Model R40 Gearmotor, 2/1 hp, 1725/850 rpm, 30/12 rpm (final), 230 V, 0.62/0.52 amps, 60 Hz, 3 phase. Inlets: (1) 1 in. threaded fitting (in-feed), (5) 1-1/4 in. dia. NPT male, (jacket), (1) 1-1/2 in. dia. threaded (infeed), (1) 1-1/2 in. dia. ferrule (sprayballs), (1) 3 in. dia. threaded fitting (infeed). Outlets: (1) 2 in. dia. pipe (jacket), (1) 2 in. dia. vent, (1) 2 in. dia. threaded bypass valve (tank). Overall dimensions: 7 ft. 7 in. L x 6 ft. 7 in. W x 10 ft. H.



