

Stainless Steel Horizontal Jacketed Tank- 2000 Gallon

Mfg:

Model:

Stock No. HDTD094.2a

Serial No.

Stainless Steel Horizontal Jacketed Tank- 2000 Gallon. Inside straight-wall dimensions: 7 ft. dia. x 6 ft. L. Percent coldwall: 25 %. Tank features a horizontally-mounted agitator with a 1 ft. 3 in. dia. propeller. (1) 5-1/2 in. dia. sight glass. Master Gearmotor, 1 hp, 1725 rpm, 144 rpm (final), 208-220-240 V, 3.6-1.8 amps, 60 cycles, 3 phase. Inlets: (1) 3/4 in. dia. FNPT (thermowell), (1) 1-1/4 in. FNPT (jacket), (1) 1-1/2 in. ACME fitting (sprayball). Outlet: (1) 3/8 in. dia. port (sample), (1) 1-1/4 in. dia. NPT (pressure relief), (1) 1-1/4 in. dia. NPT (jacket), (1) 2 in. dia. threaded (vent), (1) 2 in. dia. threaded bypass valve (tank), (1) 4-1/2 in. dia. threaded (vent). Overall dimensions: 12 ft. L x 7 ft. 6 in. W x 8 ft. 2 in. H.







