

Waukesha 25 Positive Displacement Pump

Mfg: Waukesha

Model: 025

Stock No.: HDUL965A.4

Serial No.: DO45666SSR1

Used Waukesha Positive Displacement Pump. Model 25 (DO Series). Serial: DO45666SSR1. Displacement per revolution: 0.06 gallons. Max speed / pressure: 600 RPM / 150 PSI. Nominal capacity to 36 GPM. Nominal temperature range: -40F to 300F. US Varidrive motor: 1.5 HP: 208-220/440V, 5.9-5.8/2.9 Amps, 1800 RPM, 3-phase, 60 Hz. Final RPM: 104 to 520 RPM (adjustable). Includes pump with pressure relief faceplate, vari-drive, base, and motor starter. Ports: 1.5 in. S-line fittings. Overall dimensions: 4 ft. L x 1 ft. 6 in. W x 2 ft. 9 in. High.





