

Tri Clover PR60 Positive Displacement Pump

Mfg: Tri-Clover

Model: PR60

Stock No.: HDUL967B.7

Serial No.:

Used Tri Clover Rotary Lobe Positive Displacement Pump. Model: PR60. Pump maximum flowrate: 60 GPM at 20 PSI. Displacement per revolution: 0.175 gallons. US Electric Motor: 5 HP, 1745 RPM, 208/230/460V, 3-phase, 60 Hz, TE enclosure (also rated for 190/380V 50 Hz). Ports: 3 in. Tri-Clamp. Overall dimensions: 3 ft. 7 in. L x 1 ft. 4 in. W x 1 ft. 8 in. High.





UNIMOUNT® 125

ENCLOSED
HIGH EFFICIENCY
MOTOR MODULE

13 1/4" NEMA 3 H7 60 RPM 1745 DES 7

35 TYPE UTP ENCL 1E SF1 CODE 85.5

108-27 1/160 ID Y03Y016R1107 CLA

1.0-2 16/6.8 SHAFT
6 7/8.35 END BRG 6205-2Z DUTY:CONT
END BRG 6205-2Z DUTY:CONT



7 3/4" 50HZ

15.8/7.9 AMP MAX AT 100/300V 50/60HZ
ALTERNATE RATINGS
60°C AMB 1.15 SF CLASS 9
50°C AMB 1.15 SF CLASS 9



ELECTRICAL MOTORS
DIVISION OF EMERSON ELECTRIC CO.
ST. LOUIS, MO
MADE IN U.S.A. 331841-632

