

## Tri Clover PR125 Positive Displacement Pump

**Mfg: Tri-Clover**

**Model: PRR125-3M-UH4-LS-S**

**Stock No.: HDUL975B.12a**

**Serial No.: T1308J**

Used Tri-Clover Rotary Lobe Positive Displacement Pump. Model: PRR125-3M-UH4-LS-S. Serial: T1308J. Ladish Co. Maximum pump flowrate: 120 GPM at 20 PSI. Pump displacement per revolution: 0.3 gallons. Includes: stainless steel 4-lobe rotors, pressure relief faceplate cover, cart. US Motors: 7.5 HP, 1745 RPM, 208-230/460V, 25/12.5 amps, 3-phase, 60 Hz, TE enclosure. Ports: 3 in. Tri-Clamp. Overall dimensions: 5 ft. L x 1 ft. 7 in. W x 3 ft. 11 in. High.





