

## Perma-San Pressure Wall Processor Tank- 1000 Gallon

Mfg: Perma-San

Model: JOVS

Stock No. HEC002.

Serial No. 35839

Perma-San Pressure Wall Jacketed Processor Tank-1000 Gallon. Model: JOVS. S/N: 35839. Nat'l Bd: 4023. 316 stainless steel. Sloped bottom. Bridge and covered top, 2/3 fixed cover. Blade-style agitator, with (8)12 in. L x 1-1/2 in. W blades. Mild steel bridge. Reliance Electric Motor, 5 hp, 1730 rpm, 230/460 V, 14/7 amps, 60 Hz, 3 phase. XLO Cone Motor Drive, 10 ratio, 173 rpm (final). Inlets: (2) 3 in. dia. top Q-line clamp ports. Outlets: (1) 1-1/2 in. dia. clamp outlet for jacket, (1) 1/2 in. dia. thermowell. Side and bottom water jacket rated for 90 psi @ 333°F. Shell and head thickness: 0.134 in. Overall dimensions: 76 in. L x 72 in. W x 98 in. H.



