

## Vilter 12-Cylinder Reciprocating Compressor - 120 HP

Mfg: Vilter

Model:

Stock No. JG-FB01.

Serial No.

Vilter 12-Cylinder Reciprocating Compressor - 120 HP. Refrigerant: Ammonia / Freon. Liquid-cooled heads. Shell and tube oil cooler. Lincoln Lincguard Electric Motor, 125 hp, 1770 rpm, 230/460 V, 288/144 amps, 60 Hz, 3 phase. Drive pulley diameter: 13 in. Gear pulley diameter: 21 in. Inlets: (1) ½ in. dia. port (liquid), (1) 5 in. dia. globe valve (refrigerant suction). Outlets: (1) ½ in. dia. port (liquid), (2) 3 in. dia. globe valve (refrigerant discharge). Overall dimensions: 6 ft. 11 in. L x 6 ft. 4 in. W x 4 ft. 7 ½ in. H.





