

Chemetron Process Votator- 6x48.

Mfg: Chemetron

Model: 2E648A

Stock No. JME1.

Serial No. 79505v2

Chemetron Process Votator- 6x48. Model: 2E648A. S/N: 79505v2. Scraper dimensions: 6 in. L x 2 in. W. Jacketed Tube, Model: 10191, S/N: A3427, shell MAWP @ 375 ° F: 400 psi, jacket MAWP @ 375 °F: 150 psi. Reliance Electric Motor, 7.5 hp, 1,755 rpm, 230/460 volt, 21/10.5 amps, 60 hz, 3 ph. Reliance Electric Motor Drive, 20.9 ratio , 83 rpm (final), 5,598 in. lbs torque. Inlets: (1) 1-1/2 in. dia. Q-line fitting (product), (1) 2-1/2 in. dia. (media) 4-bolt square flange with 3/4 in. dia. attachment holes at a center-to-center distance of 5-1/2 in. Outlets: (1) 1-1/2 in. dia. (media) 4-bolt square flange with 1/2 in. dia. attachment holes at a center-to-center distance of 3-1/2 in., (1) 5 in. dia. pipe (product) with a 9 in. dia. flange and (8) 3/4 in. dia. attachment holes at a center-to-center distance of 7-1/2 in. Overall dimensions: 10 ft. L x 27 in. W x 51 in. H.



