

Tonko Stainless Steel Bottle Washer/Rinser

Mfg: Tonko

Model:

Stock No. 125.JRW73.25

Serial No.

Tonko Stainless Steel Bottle Washer/Rinser. Maximum aperture/clearance: 4 in. W x 13 in. H. Sew-Eurodrive Motor, 5 hp, 1680 rpm, 230/460 V, 13.6/ 6.8 amps, 60 Hz, 3 phase. Sew-Eurodrive Gear Drive, 9.27 ratio, rpm in/out: 1680/181. Sew-Eurodrive Motor, 0.5/0.75 hp, 2250/450 rpm, 230/460 V, 3.05/1.53 amps, 60 Hz, 3 phase. Sew-Eurodrive Gear Drive, 10.31 ratio, 2250/450 rpm in, 218/44 rpm out. Conveyor infeed height: 4 ft. Conveyor exit height: 8 ft. 5 in. Overall dimensions: 23 ft. 5 in. L x 3 ft. 10 in. W x 9 ft. 9 in. H.





