

Cooled Chiller 150 Ton Model 30GT-245A-610KA

Mfg: Carrier

Model: 30GT-245A-610KA


Stock No. KVRD01.

Serial No. 0796F91850

Carrier Air Cooled Chiller 150 Ton. Model 30GT-245A-610KA (there was a 100 ton unit split away from this system now making the model the same as a 30GT-145). S/N 0796F91850. Factory Charged R22. Design Test Pressure High/Low: 450 psi/278 psi (3103 KPa/1917 KPa), respectively. Fan Motors (10): 1 hp, 460 Vac, 60 Hz, 3 phase, FLA 2.8, 1 hp, .746 KWatt (out). Power Supply 460 volt, 60 Hz, 3 phase. Permissible Voltage at Unit 506 max/ 414 min. Control Power Supply 115 volts, 60 Hz, 30 Amps, 1 phase. (2) Compressors with Model 06EF265310 and S/N 4795J01608 and 4795J01607, respectively. (2) Compressors with Model 06E6299310 and S/N 0696J00962 and 5195J03048. (1) Compressor Model number 06ET299-360, S/N 2999ME1230. Compressor Specifications: 208/230/460-400 Volt (Volt min/max 187/264/414/528/342-457), 60-60/50 Hz, 3 phase. Overall Dimensions 92 in. W x 253 in. L x 97 in. H.







SECTION A OF 2-PIECE UNIT

30GT-245A--610KA
0796F91850

UNITED TECHNOLOGIES CARRIER

MODEL	30GT-245A--610KA		SERIAL		0796F91850		FACTORY CHARGED				
DTV	VOLTS AC	PH	HZ	RLA	LRA	RELEASING # 22					
COMP 1	460	3	60	44.9	223	143 LBS	81.7	8.0			
COMP 2	460	3	60	75.7	345	144 LBS	65.3	8.0			
COMP											
DESIGN / TEST PRESSURE GAGE		HIGH	PSI	450	kPa	3103	LOW	PSI	278	kPa	1917
FAN MOTOR(S)	DTM	VOLTS AC	PH	HZ	FLA	HP	KW OUT				
OUTDOOR	4	460	3	60	3.8	1	.746				
OUTDOOR	6	460	3	60	2.7	1	.746				
OTHER											
HEATERS											
TOTAL ONLY SUITABLE FOR OUTDOOR USE											
TEMP	460	VOLTS	3	PH	60	MIN CIRCUIT AMPS	MAX FUSE AMPS				
OUTDOOR	206	MAX	414	MIN	1	532.4	400 FUSE/INCH WIRE				
INDOOR	115	MAX	1	MIN	30	AMP	FUSE/INCH WIRE				

MADE IN U.S.A. FRAME SPEED PER INSTALLATION INSTRUCTIONS 09V4454512



NAT'L. BOARD NO. 11215

CERTIFIED BY
CARRIER MEXICO S.A. DE C.V.

MAX. ALLOWABLE WORKING PRESS.

SHELL SIDE		TUBE SIDE	
W	X	PSI	AT X
	X	kPa	AT X
		278 PSI	AT 125 °F
		1917 kPa	AT 51.7 °C
MIN. DESIGN METAL TEMP.			
	X	°F	AT Y
	X	°C	AT X
		PSI	AT 278
		kPa	AT 1917

YEAR BUILT 1993 SERIAL 0496X11592

MODEL 10HB402-056-01 STATE OR C.R.N. K 6022 56

PNEUM. TEST PRESSURE 2400 kPa

SHELL SIDE EXEMPT PER U1 • C6

MADE IN MEXICO 99NA506769-056

