

Reco / Howden WGRB-204/1.65 Rotary Screw Booster Compressor Package – 150 HP

Mfg: Reco / Howden

Model: WGRB-204/1.65

Stock No: KWBF185.40

Serial No: S-1691-1

Reco / Howden WGRB 204/1.65 Rotary Screw Booster Compressor Package. Model: WGRB 204-1.65. S/N: S-1691-1. Refrigerant: last used with R-717. Howden rotary screw compressor, S/N: MK2/WGRB204/16536/036, Contract No: JH0750, gear ratio: 1.298. Booster max psi 150. Vi setting: 3.6. Displacement: 853 cfm. Reco oil separator, Nat'l bd: 3260, S/N: S-1632-1-5, MAWP: 150 psi @ 300°F, shell thickness: .250 in., head thickness: .250 in., radius: 2:1 elliptical ends. Viking oil pump, Model: AK195, S/N: 1522936. Dayton pump motor, 3 hp, 1150 rpm, 230 V, 9.6 amps, 60 Hz, 3 phase. Reco control panel. Toshiba motor, 150 hp, 3540 rpm, 230/460 V, 348/174 amps, 60 Hz. 3 phase. Overall dimensions: 15 ft. L x 5 ft. 11 in. W x 11 ft. 2 in. H. Compressor run time: 19,205.6 hrs. (ACN800).







