

## Reco Evaporative Condensing Tower – 1165 Tons

Mfg: Reco

Model: RA-1712

Stock No: KWBF212



Serial No: 791840

Reco Evaporative Condensing Tower. Model: RA-1712. Serial No: 791840. Belt No: 2B-120. Rated capacity: 1165 tons using R-22 at 105°F condensing, 40°F suction and 78°F wet bulb temperatures. 839 tons using R-717 at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. Coil pressure: 350 psi. Number of axial fans: 6. Fan diameter: 5 ft. (4) fan motors: U.S. electric motors: 20 HP, 3 phase. (2) Centrifugal pump. Model: 600, (2) Marathon electric pump motors: 3 phase. Inlets: (2) 1 ft. 8 in. manway ports, (6) 4 in. dia. ports, (2) 2 in. dia. ports. Outlets: (6) 4 in. dia. ports. Overall dimensions: 39 ft. 8 in. L x 11 Ft. W x 20 ft. H. (BH).









The Following Pictures are the Units Previous Installation.

