

FMC 100 Stainless Steel Paddle Pulper/Finisher

Mfg: FMC

Model: 100

Stock No. 125.L63000.8a

Serial No. CM 1633

FMC 100 Paddle Pulper/Finisher. Model: 100, S/N: CM 1633. Stainless steel. Cylindrical screen chamber: 18 in. dia x 36 in. L. Tyler mesh size: 14. (4) paddles. Product intake: 4 in. dia. Liquid outlet: 2-1/2 in. Pomace outlet: 9 in. L x 5 in. H. US motor: 20 hp, 220/440 V, 52/26 amps, 60 Hz, 3 phase. Final speed: 690 rpm. The FMC 100 Paddle Pulper/Finisher reduces tomatoes, fruits and vegetables to a semi-liquid or liquid state. Pits are eliminated from stoned fruit pulp and seeds, skins, and extraneous particulate materials are separated from pureed pulp with the FMC 100 Paddle Pulper/Finisher. Overall dimensions: 97 in. L x 43 in. W x 54 in. H.



