

North Star Ice M10 Flaked Ice Maker

Mfg: North Star Ice Equipment

Model: M1080S4

Stock No: LYNT002

Serial No: 4941

North Star Ice M10 Flake Ice Maker. Model: M1080S4. S/N: 4941. Nat'l Bd: 2665. Stainless steel construction. Capacity: 4.0 tons/day at -25 °F evaporator temperature and 60 °F water supply temperature. Refrigerant: Freon. MAWP @ 300 °F: 150 psi. Head thickness: 0.625 in. Dayton Motor, 1/3 hp, 1140/950 rpm, 208-230/460 V, 1.7-1.8/0.8 amps, 60/50 Hz, 3 phase. Electra Dresser Motor Drive, 50 ratio, 22.8/19 rpm (final). Makes ice from fresh water, seawater or other liquids. Stainless steel water path components make the unit approved for use in USDA-inspected meat and poultry plants and for other food processing applications. Inlets: (1) 1/2 in. dia. pipe (water), (1) 1 in. dia. pipe (media). Outlets: (1) 1/2 in. dia. pipe (media), (1) 2-1/2 in. dia. pipe (waste water), (1) 18 in. dia. discharge. Overall dimensions: 48 in. L x 38 in. W x 48 in. H.





