

Bohn / Heatcraft BR Series Air Cooled Freon Condenser - 40 Tons

Mfg: Heatcraft

Model: BRQ064

Stock No: LYNT2001E

Serial No: T02A00653

Bohn / Heatcraft BR Series Air Cooled Freon Condenser. Model: BRQ064. S/N: T02A00653. Part: 83500701. This unit was used in a research unit for a one month test. Capacity (R22 with 20 degree TD): 37.333 TR (448,000 BTUH). Ratings for R-404a and R-507 also listed. Fan Configuration: 2x2. CFM: 21,800. Volts: 230/460V, 60Hz. FLA: 14.1/7.0 Ports: (2) 1.625. Fan motor watts: 1720. Note that two motors are 0.5 HP and two are 0.75 HP (ratings listed are for 0.5 HP 540 RPM motors). Sound level: 59 DBA at 10 ft. Design Pressure 400 Psi (High Side). Weight: 1,760 lbs. Overall Dimensions: 121 in. Long x 80 in. Wide x 48 in. High.



