

APV / Crepaco R series Positive Displacement Pump

Mfg: APV/Crepaco

Model: 4R

Stock No: MDBC049

Serial No: 11662

APV / Crepaco R-Series Positive Displacement Pump. Model: 4R. S/N: 11662. Flow rate for new pump is 70 gpm with required horsepower and pressure at 80 psi. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Stainless steel pump body with vented cover. Leeson motor: 5 hp, 1740 rpm, 208-230/460 V, 13.4/6.7 amps, 60 Hz, 3 phase. Belt drive unit, driver pulley: 4-1/2 in. dia. Driven pulley: 1 ft. 1-3/4 in. dia. Ratio: 3.05. Final rpm: 570. Inlet/Outlet. (2) 2 in. ACME fitting. Includes spare rotors.(ACN74a).



