

Biro Vertical Meat Band Saw

Mfg: Biro

Model: 3334

Stock No: MDFC030.2a

Serial No:

Biro Vertical Meat Band Saw. Model: 3334. Manual slide table. Uses a 124 in x 5/8 in. x 0.22 in. saw blade. Dayton electric motor, 2.0 hp, 1735 rpm, 208-230/460 V, 5.8-5.7/2.8 amps, 60 Hz, 3 phase. Driver pulley: 5 in. diameter. Driven pulley: 11-1/2 in. diameter. Ratio: 2.3. final rpm: 754. Overall dimensions: 4 ft. 2 in. L x 2 ft. 11-1/2 in. W x 5 ft. 11 in. H.







Do not use eyebolts or lifting hooks to lift anything except the product. 931900

Dayton Industrial Motor **UL** E47479 **CS**

MODEL NO. 3KH27B VOLTS 208-230/460
 2.90 RPM 1735 AMPS 5.8-5.70/2.80
 3 FRAME 145T TYPE FUT - SFA
 1.15 HZ 60 NEMA DESIGN B CLASS F
 TE MB 40 C LR KVA CODE 11
 DUTY CONT. POW. FACTOR 75.3 NEMA NOM. EFF. 84.0
 1.20 ENR 6205 END BRG. 6203
 005-BK16-11 00 040A

To reverse rotation interchange any two line leads.

94501

SPECIAL FEATURES
 AMP. MAX. 208V. 26HZ. 6.7

Do not use eyebolts or lifting hooks to lift anything except the product. 931900

Dayton Industrial Motor **UL** E47479 **CS**

MODEL NO. 3KH27B VOLTS 208-230/460
 2.90 RPM 1735 AMPS 5.8-5.70/2.80
 3 FRAME 145T TYPE FUT - SFA
 1.15 HZ 60 NEMA DESIGN B CLASS F
 TE MB 40 C LR KVA CODE 11
 DUTY CONT. POW. FACTOR 75.3 NEMA NOM. EFF. 84.0
 1.20 ENR 6205 END BRG. 6203
 005-BK16-11 00 040A

To reverse rotation interchange any two line leads.

94501

SPECIAL FEATURES
 AMP. MAX. 208V. 26HZ. 6.7

