

Cherry-Burrell Stellar Series Superhomo Homogenizer


Mfg: Cherry-Burrell

Model: SS-2100 UBR Stellar Series


Stock No.: MHCR038.13

Serial No.: 731624






Cherry-Burrell Stellar Series Superhomo Homogenizer. Model: SS-2100 UBR Stellar Series. S/N: 731624. Capacity: 930 gph. 2-stage manual valve assembly. 1-1/4 in. dia. plungers. Spring loaded poppet valve cylinders. Working pressure: 3000 psi. Toshiba Electric Motor, 30 hp, 1755 rpm, final rpm: 365, 230/460 V, 73/36.5 amps, 60 Hz, 3 phase. Gear pulley diameter: 24 in. Motor pulley diameter: 5 in. Pulley ratio: 4.8. Inlets: (1) 2 in. dia. ACME fitting. Outlets: (1) 2 in. dia. S-Line fitting. Overall dimensions: 4 ft. 2 in. L x 2 ft. 7 in. W x 4 ft. 2 in H. (ACN640)











TOSHIBA

HIGH EFFICIENCY
ELECTRIC
3 φ INDUC MOTOR

CONNECTIONS	MODEL NUMBER:	0304TSA23A-P		INS. CLASS	F	DUTY
9 5 11 3	HP/KW	3.7/2.2		NEMA CODE	16	ENCL.
7 12 1	VOLTS	230/400 V		NEMA DESIGN	B	TYPE
VOLTAGE	AMPS	73/36.5 A		MEETS IP	54	FORM
8	RPM	Hz	60	OPP. END BRG.	6210	
5 7	P.F.	S.F.	1.1	DRIVE END BRG.	6310	
VOLTAGE	NOM. FL. EFF.	0.84		SERIAL NO.	63524	
12 1	MOTOR WT.	LBS.	kg.	30 HP 80.7 A		
3	MAX. AMB.	40 °C USABLE@208V				

