

Morris / ITT Goulds RX Heavy Slurry Pump

Mfg:

Model: 2RX

Stock No: MRD653.a

Serial No: M-21058

Morris / ITT Goulds RX Heavy Slurry Pump Model: 2RX. S/N: M-21058. The Goulds RX side-suction slurry pumps are designed for handling highly abrasive slurries. The suction/discharge ports can be rotated into different positions for ease of installation. Unit features replaceable wear liners, heavy duty frame, external impeller adjustments, etc. Common applications include: bauxite, wet process cement, lime slurry, dust collection systems, sand, chemical sludges, plate wastes, etc. The pump size 2x4x15.5 pumps up to 250 GPM at 250 feet of head (1750 RPM max). Westinghouse Life-Line T Motor, 15 HP, 1755 RPM, 230/460V, 39/19.5 amps, 60 Hz, 3-phase. Inlets: (1) 4 in. dia. flanged port. Outlets: (1) 2 in. dia. flanged port. Overall dimensions: 49 in. L x 28 in. W x 44-1/2 in. H. (ACN377).



