

## Waukesha 30 Positive Displacement Pump

Mfg: Waukesha

Model: 30

Stock No: MRDC0033.19a

Serial No: 17066 SS

Waukesha Positive Displacement Pump. Model 30. S/N: 17066 SS. Flow rate for new pump is 36 GPM with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (2) 4-3/8 in. rotors. Sew Eurodrive for motor: (1700/20.91 ratio), final rpm: 169. Sew Eurodrive motor: 3 hp, 1700 rpm, 230/460 volts, 8.6/4.3, 60 Hz, 3 phase. Square D enclosure, type SCW11, class 9991 containing an Allen Bradley motor control, no. A10BNO. (1) 1-1/2 in. ACME inlet. (1) 1-1/2 in. ACME outlet. Overall dimensions: 4 ft. 7-1/2 in. L. x 1 ft. 3-7/8 in. W. x 2 ft. 11 in. H.



