

Tri Clover Centrifugal Pump

Mfg: Tri Clover

Model: C114MD56T-S

Stock No: MRDC0115.4

Serial No: R1523

Tri Clover Centrifugal Pump. Model: C114MD56T-S. S/N: R1523. Flow rate for new pump is 50 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller size: 3-1/4 in. Reliance electric motor: 1hp, 1725 rpm, 230/460 volts, 4.4/2.2 amp, 3 ph, 60 Hz. (1) 2 in. S-line inlet. (1) 1-1/2 in. S-line outlet. Overall dimensions: 2 ft. 9 in. L. x 1 ft. 5-1/8 in. W. x 2 ft. 11-5/8 in. H.(ACN39).





