

2004 IDEX Corporation Jun-Air Compressor

Mfg: IDEX Corporation Jun-Air®

Model: 8000-150B

Stock No: MRDC1080.5

Serial No: 577438

2004 IDEX Corporation Jun-Air® Compressor. Model: 8000-150B. Serial No: 57743B. Displacement: 29.95 CFM. Tank capacity: 39.6 gallons. Noise level: 80 dB (A)/lm. System power requirements: 230 V, 12 amps, 60 Hz, 3 phase. (4) motors with a total of (8) pistons. Maximum pressure: 120 psi. (4) Jun-Air motors, 1.5 hp (1.10 kW), 1670-1730 rpm, 220-270 V (delta), 6.40-5.0 amps, 60 Hz, 3 phase. JUN-AIR compressors are ideal within many applications. They are quiet in operation and provide clean, compressed air. In addition, all JUN-AIR compressors have a unique design and are updated with the latest technology, making them suitable for use in an increasing number of applications including use in dental clinics, laboratories, dispensing systems, graphics, health care, door opening devices and fitness equipment. Overall dimensions: 4 ft. 7 in. L x 2 ft. 7 in. W x 2 ft. 10 in. H.





