

Vilter 440 8-Cylinder Reciprocating Compressor - 100 HP

Mfg: Vilter

Model: 448

Stock No.: NMCC197

Serial No.: F30355

Vilter 440 Series 8-Cylinder Reciprocating Compressor. Model: 448. Serial: F30355. WEG electric motor: 100 HP, 208-230/460V, 1780 RPM, 60 Hz, 3-phase, 404T/5T frame (also rated for 50 Hz). Overall dimensions: 6.5 ft. L x 4 ft. 2 in. W x 5 ft. H.



WEG		NEMA Premium		Inverter Duty Motor	
C020294		175ETW 1008200867		404/5T	
PH	3	HP(NM)	100(75)	FRAME	404/5T
V	230	460	Hz	60	
A	230	115	ph	1.15	
RPM	1780	3ph		INS. CL. F	
NEMA NOM. EFF.	95.4	SI	PI	0.86	
CODE	H	DEST	B	WEG	CON
ENCL.	ODP	WEG	DP	100HP	100/150
USABLE AT 208V	100	A	SD	100HP	330V 138A 14.75

100 HP