

## Adjustable Height Conveyor

**Mfg:**


**Model:**

**Stock No: NOI1118**

**Serial No:**

Adjustable Height Conveyor. Eurodrive motor: .37 k.w., 1700 rpm, 266/460 v, 1.85/1.07 a, 60 Hz, 3 phase. Max conveyor exit height: 3 ft. 4 in. Lowest conveyor exit height: 1 ft. 5 in. Conveyor dimensions: 16 ft. L x 6-1/2 in. W. Overall dimensions: 8 ft. 2 in. L x 1 ft. 9 in. W x 4 ft. 11 in. H.





SEW EURODRIVE		NORMANTON WORKS ENGLAND	
TYPE	DET 71D4	BRAKE V	
SER	N786905	BRAKE Nm	
KW	0.37	IP	5
BPM	1700	INS. CL.	v2667460 Y
RATIO	A1.85/1.07	~	3 H20
		cos φ	0.7

GEARBOX LUBRICATED BY B.P. OIL