

Wolfking Danmark Vertical/Horizontal Screw Auger Conveyor with Hopper

Mfg: Wolfking Danmark

Model: Vertical

Stock No. NOI8014.

Serial No. 58460

Wolfking Danmark Vertical/Horizontal Screw Auger Conveyor with Hopper. Model: Vertical. S/N: 58460. Auger: 8-1/2 in. dia. x 73 in. H. Discharge offset: 90°. Lincoln Motor, 15 hp, 1750 rpm, 230/460 V, 10/.20 amps, 60 Hz, 3 phase. Type: Horizontal. S/N: 58458. Maximum capacity: 2.46 cu. ft. Minimum capacity: 0.73 cu. ft. Screw auger dimensions: 10 in. dia. x 72 in L. Screw auger housing diameter: 10-1/4 in. Flender Motor, 5.5 kW, 1728 rpm, 220 V, 3 phases. The vertical screw conveyors are designed for transport of pre-ground material where the space is limited. Exit height: 67-1/2 in. (4) adjustable wheels for easy maneuverability. Inlets: (1) 10 in dia. port, (1) 51 in. L x 19 in. W (hopper infeed). Outlets: (1) 15 in. L x 13-1/2 in. W discharge, (1) 10-1/4 in. dia. discharge. Overall dimensions: 9 ft. 11 in. L x 4 ft. W x 7 ft. 10 in. H.







