

1990 Cherry-Burrell Shell and Tube Heat Exchanger – 27.35 sq. ft.

Mfg: Cherry Burrell

Model:

Stock No: NOI8026

Serial No: CR23779

1990 Cherry-Burrell Shell and Tube Heat Exchanger. S/N: CR23779. Tube material: 316 stainless steel. Number of passes: 10. Number of tubes: 19. Tube dimensions: 1 in. dia. x 5 ft. 6 in. Heat transfer surface area: 27.358 sq. ft. approximate total tube volume: 4.258 gal. MAWP: 150 psi @ 400°F. MDMT: -20°F @ 150 psi. Inlets: (1) 1 in. dia. NPT (product), (1) 2 in. dia. FNPT (media). Outlets: (1) 1 in. dia. NPT (product), (1) 2 in. dia. FNPT (media). Overall dimensions: 6 ft. 9 in. L x 2 ft. 3-1/4 in. W x 3 ft. 5-1/2 in. H.



