

Carlyle 6-Cylinder Heavy Duty Reciprocating Compressor- 33 Ton

Mfg: Carlyle




Model: 06EF299310




Stock No.: NOI8037

Serial No.: 2597J02576 and 2597J02579

(2) Carlyle 6-Cylinder Heavy Duty Reciprocating Compressors- 33 Ton. Model: 06EF299310. S/N's: 2597J02576 and 2597J02579. Mfg. No: 6EAFEC3C2H30. Refrigerant: R-22. Nominal horsepower: 40. Displacement @ 1750 rpm: 99 cfm. Suction temperature rating: -10°F to 50°F. Power supply: 208-230/460/400 V, 690/345, LRA, 50/60 Hz, 3 phase. Inlets: (1) 2 in. dia. refrigerant suction port. Outlets: (1) 1-1/2 in. dia. refrigerant discharge port. Overall dimensions: 3 ft. L x 2 ft. W x 2 ft. H.









Carlyle MODEL NUMBER 06EF299310



MFG/N 6EAFEC3C2H30 NTR C412394

VOLTS	PH	HZ	VOLTS (MIN/MAX)	RLA	LRA
208/230	3	60	187/264		690.0
480	3	60	414/528		345.0
400	3	50	342/457		345.0



MADE IN U.S.A.

S/N 2597J02576

6E2XXX

Carlyle MODEL NUMBER 06EF299310



MFG/N 6EAFEC3C2H30 NTR C412394

VOLTS	PH	HZ	VOLTS (MIN/MAX)	RLA	LRA
208/230	3	60	187/264		690.0
480	3	60	414/528		345.0
400	3	50	342/457		345.0



MADE IN U.S.A.

S/N 2597J02576

6E2XXX

Carlyle MODEL NUMBER 06EF299310



MFG/N 6EAFEC3C2H30 NTR C412394

VOLTS	PH	HZ	VOLTS (MIN/MAX)	RLA	LRA
208/230	3	60	187/264		690.0
480	3	60	414/528		345.0
400	3	50	342/457		345.0



MADE IN U.S.A.

S/N 2597J02579

6E2XXX