

## Crepaco Positive Displacement Pump

**Mfg: Crepaco**

**Model: R2R**

**Stock No: NOIP1001**

**Serial No: D-2263**

Crepaco Positive Displacement Pump. Model: R2R. S/N: D-2263. Flow rate for new pump is 6 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. (2) 3 in. rotors. Marathon Electric motor. Motor drive: 1 Hp, 1800 rpm motor input, output rpm: 370 max, 123 min, 575 V, 1.2 A, 60 Hz, 3 Phase, 4.13 Gear ratio. Inlet/outlet: (2) 1-1/2 in. Acme ports. Overall dimensions: 3 ft. 1/2 in. L x 1 ft. 3 in. W x 2 ft. 4-1/4 in. H.





