

Viking GPV Model Gear Pump – 1.5 HP


Mfg: Viking Pump, Inc. (IDEX Corp.)

Model: GPV-0758-7

Stock No.: NOIP1405

Serial No.: 10590132, 10590133, 10549139

(3) Viking Pump, Inc. (IDEX Corp.) Pumps. Model: GPV-0758-7. Serial: 10590132, 10590133, 10549139. Quantity available: 3. Motor specs: 1.5 HP, 110/220V, 17/8.5 amps, 1425 RPM, 50 Hz, 1-phase.



BALDOR®
INDUSTRIAL MOTOR

THERMALLY PROTECTED

CAT. NO.			
SPEC.	35E24-6085		
FRAME	58C	SER.	F1194
H.P.	1 1/2 TE		
VOLTS	110/220		
AMPS	17/8.5		
R.P.M.	1425		
HZ	50	PH	1 CLASS B
SER. F.	1.00	DES	L CODE J
NEMA NOM. EFF.	71 %	P.F.	84 %
RATING	400 AMB-CONT		
	2-547-409-98		

BALDOR ELECTRIC CO.
FT. SMITH, ARK.
MFD. IN U.S.A. 

H.P.	1 1/2	SER.	F1194
VOLTS	110/220		
AMPS	17/8.5		
R.P.M.	1425		
HZ	50	PH	1 CLASS B
SER. F.	1.00	DES	L CODE J
NEMA NOM. EFF.	71 %	P.F.	84 %
RATING	400 AMB-CONT		
	2-547-409-98		

BALDOR ELECTRIC CO.
FT. SMITH, ARK.
MFD. IN U.S.A.  