

APV / Crepaco Centrifugal Pump

Mfg: APV/Crepaco

Model: 18

Stock No: NOIP8029

Serial No: 18-16295

APV / Crepaco Centrifugal Pump. Model: 18. S/N: 18-16295. Flow rate for new pump is 220 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 4-3/4 in. Louis Allis electric motor, 5 hp, 3500 rpm, 230/460 V, 12.8/6.4 amps, 60 Hz, 3 phase. Inlet: (1) 2-1/2 in. dia. ACME fitting. Outlet: (1) 2 in. dia. ACME fitting. Overall dimensions: 1 ft. 9 in. L x 1 ft. 7/8 in. W x 11-3/8 in H.(ACN25).





INDUCTION

MOTOR



MODEL 7390104009

TYPE	606A	213C	FRAME
HP	5	3500	R.P.M.
W.P.S.	130 (460)	3	PHASE
W.P.L.S.	60	1.15	POWER FACTOR
V.W.C.	40	CONT	DUTY
TEMP. RISE	207.7	3078D	EMPT. EXT. MARKING
TEMP. INDEX	7	H	WIND. SYSTEM
W.P.	2-426-4	0311-1	WINDING CONNECTION

WINDING CONNECTION

WESTINGHOUSE CO. WYOMING, WIS.