

## APV Puma Sanitary Centrifugal Pump


Mfg: APV

Model:

Stock No: NOIP8292

Serial No:

APV Puma Sanitary Centrifugal Pump. Capacity: 60gpm. Impeller diameter: 6-1/2 in. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. U.S. Electric Motor, 3 hp, 1765 rpm, 208-230/460 V, 8.6-8/4 A, 60 Hz, 3 phase. Inlet: (1) 3 in. dia. S-line fitting. Outlet: (1) 2 in. dia. S-line fitting. Overall dimensions: 1 ft. 10-1/2 in. L x 1 ft. 2 in. W x 1 ft. H.





MODEL	F377A	FR	F8217	TYPE	T01	ENCL	11
SHAFT END RING	3208-22303		DRY END RING	0208-22303			
PH	3	MAX AMPS	10	°C	ID#	810-1393A-11	
ASUL CLASS	F DUTY CONT USABLE ON 208V 60HZ AT 9.0 MAX AMPS						
HP	3	RPM	1755	HP	3	RPM	1450
VOLTS	208-230/480			VOLTS	190/360		
FL AMPS	3.5+8	7A		FL AMPS	9.0/6.0		
SF	1.15			DESIGN	B		
CODE	K			DESIGN	N		
CODE	K			CODE	N		
NEMA NOM EFFICIENCY	87.5	NOM PF	79.3	NEMA NOM EFFICIENCY	85.5	NOM PF	83.3
GUARANTEED EFFICIENCY	85.5	MAX KW/B	1.4	GUARANTEED EFFICIENCY	82.5	MAX KW/B	1.2
U.S. ELECTRICAL MOTORS DIVISION OF EMERSON ELECTRIC CO. CLEVELAND, OH MADE IN MEXICO				ENERGY EFFICIENT MOTOR 0478P			

