

Buffalo "Can-O-Matic II" Ammonia Pump

Mfg: Buffalo Pumps

Model: HCR

Stock No: NSF102.2

Serial No: 87440532

Buffalo "Can-O-Matic II" Ammonia Pump. Model: HCR. S/N: 87440532. Size:H66V-2013. Capacity: 53 gpm @ 75 thd. Peerless Winsmith Motor, 10 hp, 1750 rpm, 460 V, 17.8 amps, 60 Hz, 3 phase. (1) 9 in. dia. impeller. Buffalo HCR-series pumps are single suction, single stage, hermetic centrifugal pumps designed for zero leakage by elimination of the pump stuffing box. These pumps are equipped with uniquely designed motors. Inlets: (1) 3 in. dia. flanged inlet. Outlets: (1) 1-1/2 in. dia. flanged outlet. Overall dim: 2 ft. L x 1 ft. 6 in. W x 1 ft. 9 in. H.





