

## Stainless Steel Incline Conveyor

**Mfg:**

**Model:**

**Stock No: OI122**

**Serial No:**

Stainless Steel Incline Conveyor. Maximum aperture/clearance above belt: 13-1/2 in. W x 4 in. H. Height at conveyor inlet: 27 in. Height at conveyor outlet: 71 in. Spray bridge. Baldor Industrial Motor, 1-1/2 hp, 1725 rpm, 208-230/460 V, 5.3-5/2.5 amps, 60 Hz, 3 phase. Boston Motor Drive, 43 ratio, 40 rpm (final). Outlets: (1) 18 in. L x 17 in. W discharge chute. On casters. Overall dimensions: 12 ft. 2 in. L x 3 ft. W x ft. 4 in. H.

