Boston Agitator Drive	
Mfg: Boston	Model:
Stock No. Ol168.	Serial No. F584

Boston Agitator Drive. S/N: F584. Motor specifications: 10 hp, 1,725 rpm, 122 rpm (final), 208-230-460 V, 60 Hz, 3 phase. Mounting base dimensions: 16 in L x 16 in W with (4) 3/4 in. dia. attachment holes at a center-to-center distance of 13-1/2 in. Overall dimensions: 16 in. L x 16 in. W x 32 in. H.











