

Bohn Heat Transfer Division Shell and Tube Heat Exchanger

Mfg: Bohn

Model:

Stock No. OI186.

Serial No.

Bohn Heat Transfer Division Shell and Tube Heat Exchanger. Barrel dimensions: 12 in. dia. x 10 ft. L. (208) 1/2 in. dia. heat exchanger tubes. Shell side MAWP: 250 psi @ 300°F. Tube side MAWP: 250 psi @ 300°F. Inlets: (1) 3-1/2 in. media inlet port. Outlets: (2) 3 in. ports, (1) 1/2 in. threaded male relief. Overall dimensions: 11 ft. 8 in. L x 18 in. W x 37 in. H.

